



POROUS SOLID DENSITY TESTER

The TTDS Porous Solid Density Tester is a high-precision instrument designed to measure bulk density, volume, and porosity across diverse industries. Compliant with ASTM and JIS standards, it is essential for evaluating ceramics, construction materials, and powder metallurgy.

Available in three specialized configurations—TTDSPorous IIIPA/VA, IIIB/VB, and IIIC/VC—the series caters to materials like wood, minerals, and oil-impregnated bearings. Supporting weights up to 500g, it ensures material consistency and structural integrity for critical engineering applications.

Engineered for efficiency, the tester features a five-sample memory and four unique software options. It delivers exceptional accuracy with 0.01% porosity precision and 0.001g/cm³ density precision, providing a reliable, standardized solution for professional quality control and material characterization.

APPLICATIONS

- **Ceramics and Construction Materials** – Measures bulk density and porosity in ceramic tiles, bricks, and structural components.
- **Magnetic Materials** – Evaluates density and porosity of ferrites and related magnetic products.
- **Wood and Polymers** – Tests porosity in wood, EVA, EPDM, and sponge materials for product consistency.
- **Minerals and Rocks** – Determines bulk density and porosity for geological and construction applications.
- **Refractories and Graphite** – Assesses material stability under high-temperature conditions by measuring porosity.
- **Powder Metallurgy** – Analyzes bulk density and porosity of sintered parts for strength and performance control.
- **Oil-Impregnated Bearings** – Confirms porosity levels critical for lubrication and durability in mechanical applications.
- **Research and Quality Control** – Provides standardized testing compliant with ASTM and JIS methods for material characterization.

-
- TTDSPorousIIIPA/ TTDSPorousVA: Ceramic pill, construction, magnetic material, wood
 - TTDSPorousIIIB/ TTDSPorousVB: Minerals, rocks, sponge, EVA, EPDM, refractor, graphite

- TTDSporousIIIC/ TTDSporousVC: Powder metallurgy and oil-impregnated bearing

FEATURES

- With 5 sets of memory, you can test 5 samples at one time
- Included four unique software for your choice
- Standards of Porous Solid Density Tester - TTDS-Porous Solid: ASTM C20/C134/C373/C329 ASTM D3574 ASTM B311/B328, JIS Z2505/Z2506

TECHNICAL SPECIFICATIONS

Model	TTDSporousIIIPA	TTDSporousVA	TTDSporousIIIB	TTDSporousVB	TTDSporousIIIC	TTDSporousVC
Standards	ASTM C20/C134/C373/C329		ASTM D3574		ASTM B311/B328, JIS Z2505/Z2506	
Weighting range	0.01g – 300g	0.01g – 500g	0.01g – 300g	0.01g – 500g	0.01g – 300g	0.01g – 500g
Porosity precision	0.01%					
Density precision	0.001g/cm ³					
Value showed	Bulk density, volume and porosity					



Torontech Inc.

251 Consumers Road, Suite 1200
Toronto, Ontario, M2J 4R3, Canada 

Phone: +1 416 368 2721 | Fax: +1 416 981 7652
Email: info@torontech.com

Torontech, LLC

601 Brickell Key Drive, Suite 700
Miami, FL 33131, USA 

Toll-Free: 1-866-383-7919
Email: sales@torontech.com

Torontech ME FZE

Meydan Grandstand, 6th Floor,
Meydan Road, Nad Al Sheba,
Dubai-261440, UAE 

Phone: +971 488 19252
Email: me@torontech.com

