

PARTICLE QUANTIFIER INSTRUMENT - TORONPQI™ 1000



ToronPQI™ 1000 - ASTM D8184 Compliant Ferrous Debris Monitor

The ToronPQI™ 1000 is the entry-level model in Torontech's PQI line, offering precise ferrous wear debris analysis in lubricating oils and hydraulic fluids. It utilizes the Particle Quantifier (PQ) method in accordance with ASTM D8184, ensuring standardized, repeatable, and highly accurate readings.

Compact yet powerful, the ToronPQI™ 1000 provides direct measurement of ferromagnetic particles without chemical pretreatment — delivering fast results within just 7 seconds per sample.

Compliance

- Fully conforms to ASTM D8184 - Standard Test Method for Determination of Ferrous Wear Debris in Lubricating Oils and Hydraulic Fluids by the Particle Quantifier Method.

APPLICATIONS

Applications

- Oil analysis and lubrication testing labs
- Industrial equipment and gearbox maintenance
- Power plants, steel mills, and mining machinery
- Predictive maintenance and reliability programs

Particle Quantifier Instrument - ToronPQI-1000

Particle Quantifier Instrument – ToronPQI-1000

Particle Quantifier Instrument – ToronPQI-1000

Particle Quantifier Instrument – ToronPQI-1000

FEATURES

Key Features & Benefits

- ASTM D8184 Compliance – Conforms to international PQ measurement standards.
- Fast & Direct Measurement – Analyze samples in seconds without preparation.
- High Sensitivity – Detects ferromagnetic particles $\geq 1 \mu\text{m}$.
- Repeatability – ± 4 PQ or $\pm 1 \%$ (whichever is greater).
- USB Data Export – Convenient PC connectivity for record-keeping and trending.
- Compact Design – Lightweight, bench-top footprint ideal for laboratories.

TECHNICAL SPECIFICATIONS

Parameter	Specification
Measurement Range	0 - 15 000 PQ

Parameter	Specification
Repeatability	± 4 PQ or ± 1 %
Measurement Time	Approx. 7 s per sample
Particle Detection	Ferromagnetic $\geq 1 \mu\text{m}$
Display	LCD (120 × 90 mm)
Data Output	USB interface
Voltage	AC 220 V ± 10 %, 50-60 Hz (110V is also available)
Dimensions	370 × 222 × 140 mm
Weight	≈ 3.8 kg



Torontech Inc.

251 Consumers Road, Suite 1200
Toronto, Ontario, M2J 4R3, Canada 

Phone: +1 416 368 2721 | Fax: +1 416 981 7652
Email: info@torontech.com

Torontech, LLC

601 Brickell Key Drive, Suite 700
Miami, FL 33131, USA 

Toll-Free: 1-866-383-7919
Email: sales@torontech.com

Torontech ME FZE

Meydan Grandstand, 6th Floor,
Meydan Road, Nad Al Sheba,
Dubai-261440, UAE 

Phone: +971 488 19252
Email: me@torontech.com

