



ELECTRIC PROPULSION PERFORMANCE TEST SYSTEM - TORONEPP™ 2000

Electric Propulsion Performance Test System - ToronEPP™ 2000

ToronEPP™ 2000 is a high-capacity Electric Propulsion Performance Test System specifically engineered for the rigorous evaluation of Hall thrusters. By utilizing an expansive vacuum chamber and a versatile platform footprint, the system effectively mitigates background-pressure interference, ensuring high-fidelity propulsion measurements.

It is optimized to maintain stable, high-vacuum conditions even under significant xenon or krypton propellant flow. This makes it an ideal solution for R&D labs requiring a repeatable, data-driven environment for complex instrumentation and long-duration testing campaigns.

APPLICATIONS

Electric Propulsion Performance Test System - ToronEPP™ 2000

Applications

- Hall thruster evaluation under controlled vacuum conditions
- Performance mapping and comparative benchmarking across thruster designs
- Operating stability studies during higher propellant flow and extended runs
- Test development for electric propulsion programs and subsystem verification
- Repeatable lab testing where background pressure control impacts results



FEATURES

Electric Propulsion Performance Test System - ToronEPP™ 2000 Key Features

- S30408 stainless steel chamber construction supports corrosion resistance and long service life
- Larger vacuum chamber supports flexible Hall thruster setups and expanded diagnostics access
- Defined ultimate pressure performance supports stable baseline vacuum conditions
- Operating pressure capability maintained during higher propellant flow for repeatable testing
- Test platform supports stable installation and repeatable alignment during measurements

TECHNICAL SPECIFICATIONS

Electric Propulsion Performance Test System - ToronEPP™ 2000 Technical Specification

Specification	Details
Chamber Dimensions	φ 2000 mm × 4000 mm
Platform Dimensions	L 1200 mm × W 1000 mm
Ultimate Pressure	12 h $\leq 5.0 \times 10^{-5}$ Pa
Operating Pressure	$\leq 5.0 \times 10^{-3}$ Pa (with xenon gas flow rate of 5.41 mg/s, krypton gas flow rate of 5.5 mg/s, and argon pumping capability)



Torontech Inc.

251 Consumers Road, Suite 1200
Toronto, Ontario, M2J 4R3, Canada 🇨🇦

Phone: +1 416 368 2721 | Fax: +1 416 981 7652
Email: info@torontech.com

Torontech, LLC

601 Brickell Key Drive, Suite 700
Miami, FL 33131, USA 🇺🇸

Toll-Free: 1-866-383-7919
Email: sales@torontech.com

Torontech ME FZE

Meydan Grandstand, 6th Floor,
Meydan Road, Nad Al Sheba,
Dubai-261440, UAE 🇦🇪

Phone: +971 488 19252
Email: me@torontech.com

